



SB 18 LT BL

- Brushless cordless hammer drill with optimal power for demanding applications
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- High-performance impact mechanism for optimum drilling performance
- Integrated working light to illuminate the contact area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

| Order no. | 602316500 |
|-----------------------------|-----------------------------|
| EAN code | 4007430326324 |
| Type of battery pack | Li-Power |
| Battery voltage | 18 V |
| Battery pack capacity | 2 x 4 Ah |
| Maximum torque, soft | 34 Nm / 301 in-lbs |
| Maximum torque, hard | 75 Nm / 663.8 in-lbs |
| Adjustable torque | 0.7 - 8 Nm // 6 - 71 in-lbs |
| Drill-Ø masonry | 13 mm / 1/2 " |
| Drill Ø steel | 13 mm / 1/2 " |
| Drill-Ø soft wood | 38 mm / 1 1/2 " |
| No-load speed | 0 - 600 / 0 - 2100 rpm |
| Maximum impact rate | 31950 bpm |
| Chuck capacity | 1.5 - 13 mm // 1/16 - 1/2 " |
| Weight without battery pack | 1.2 kg / 2.6 lbs |
| Weight with battery pack | 1.9 kg / 4.2 lbs |

Scope of delivery

Keyless chuck, Belt hook and bit case, 2 Li-Power battery packs (18 V/4.0 Ah), Charger ASC 55 "AIR COOLED", metaBOX 145