



03/2018

# Oil Filter Tool Series



KL-0122-Series..



# www.gedore-automotive.com

#### **GEDORE Automotive GmbH**

78166 - Donaueschingen Postfach 1329 78154 Donaueschingen - GERMANY

Breslauer Straße 41

T +49 (0) 771 / 8 32 23-0 F +49 (0) 771 / 8 32 23-90 info.gam@gedore.com www.gedore-automotive.com

#### **GEDORE WELTWEIT / GEDORE WORLDWIDE**

Weltweite GEDORE Servicestellen / Niederlassungen finden Sie im Internet unter: www.gedore.com Worldwide GEDORE service centers / offices are listed on the Internet at: www.gedore.com

#### GEDORE TOOLS, INC.

Only for USA, Canada & Mexico Sólo para EE.UU., Canadá y México Seulement pour les USA, le Canada et le Mexique

7187 Bryhawke Circle, Suite 700 North Charleston, SC 29418, USA Phone +1-843 / 225 50 15 Fax +1-843 / 225 50 20 info@gedoretools.com






# **KL-0122-..Oil Filter Tool Series**

In order to identify the suitable oil filter socket, proceed as follows:

- 1. Check whether the filter has flats or ribs.
- 2. Count the number of flats or ribs.



4. Choose the suitable oil filter socket with the help of the **Overview Table** below

Size	Size (width across flats)	Part No.	Description
27mm	27mm waf	KL-0122-52	Oil Filter Socket
32mm	32mm waf	KL-0122-51	Oil Filter Socket
36mm	36mm waf	KL-0122-5	Oil Filter Socket
64mm	64mm waf, 14 flats	KL-0122-308	Oil Filter Socket
65mm	65mm waf, 14 flats	KL-0122-309	Oil Filter Socket
66mm	66mm Ø, 6 ribs	KL-0122-318	Oil Filter Socket
66mm	66mm Ø, 6 ribs	KL-0122-601	Oil Filter Socket
67mm	67mm waf, 14 flats	KL-0122-311	Oil Filter Socket
72mm	72mm waf, 14 flats	KL-0122-310	Oil Filter Socket
73mm	73mm waf, 10 flats	KL-0122-612	Oil Filter Socket
74mm	74mm waf, 14 flats	KL-0122-301	Oil Filter Socket
74mm	74mm waf, 14 flats	KL-0122-3	Oil Filter Socket
74mm	74mm waf, 15 flats	KL-0122-302	Oil Filter Socket
74 mm	74mm waf, 30 ribs	KL-0122-306	Oil Filter Socket
74mm	74mm waf, 8 flats	KL-0122-323	Oil Filter Socket
76mm	76mm Ø, 12 ribs	KL-0122-219 B	Oil Filter Socket,
76mm	76mm Ø, 12 ribs	KL-0122-319	Oil Filter Socket
76mm	76mm Ø, 12 ribs	KL-0122-7	Oil Filter Wrench
76mm	76mm waf, 15 flats	KL-0122-303	Oil Filter Socket
78mm	78mm waf, 15 flats	KL-0122-332	Oil Filter Socket
79mm	79mm waf, 15 flats	KL-0122-305	Oil Filter Socket
82mm	82mm waf, 15 flats	KL-0122-314	Oil Filter Socket


Size	Size (width across flats)	Part No.	Description
84mm	84mm waf	KL-0122-609	Oil Filter Socket
86mm	Ø 86mm 18 ribs	KL-0122-312	Oil Filter Socket
86mm	Ø 86mm 18 ribs	KL-0122-212	Oil Filter Socket, Aluminium
86mm	86mm waf, 16 flats	KL-0122-326	Oil Filter Socket
86 mm	86mm waf, 16 flats	KL-0122-426	Oil Filter Socket,
89 mm	89mm waf, 15 flats	KL-0122-315	Oil Filter Socket
91mm	91mm waf, 15 flats	KL-0122-304	Oil Filter Socket
92mm	92mm waf, 10 flats	KL-0122-324	Oil Filter Socket
92mm	92mm waf, 36 ribs	KL-0122-307	Oil Filter Socket
93mm	93mm Ø, 45 ribs	KL-0122-317	Oil Filter Socket
93mm	93mm Ø, 45 ribs	KL-0122-217	Oil Filter Socket,
95mm	95mm waf, 15 flats	KL-0122-334	Oil Filter Socket
96mm	96mm Ø,18 ribs	KL-0122-313	Oil Filter Socket
96mm	96mm Ø,18 ribs	KL-0122-213	Oil Filter Socket,
99mm	99mm waf, 15 flats	KL-0122-335	Oil Filter Socket
100mm	100mm waf, 15 flats	KL-0122-316	Oil Filter Socket
103mm	103mm waf, 14 flats	KL-0122-611	Oil Filter Socket
106mm	106mm waf, 15 flats	KL-0122-322	Oil Filter Socket
108mm	108mm Ø, 18 ribs	KL-0122-321	Oil Filter Socket
108mm	108mm Ø, 18 ribs	KL-0122-602	Oil Filter Socket
108mm	108mm waf, 15 flats	KL-0122-327	Oil Filter Socket

# **Warnings and Notes**

 Any work on vehicles should only be performed by qualified specialist personnel observing and complying with the directions, provisions, and safety regulations specified by the vehicle manufacturer!

**GEDORE** 






# KL-0122-332 Oil Filter Socket, Size 78mm waf

Applicable to Ford, Mitsubishi, Nissan, Toyota etc.

Suitable for use on oil filters with size 78mm waf and 15 flats.

# KL-0122-334






# KL-0122-334 Oil Filter Socket, Size 95mm waf

Applicable to Alfa Romeo, Chrysler, Ford, Toyota etc.

Suitable for use on oil filters with size 95mm waf and 15 flats.

### KL-0122-335





# KL-0122-335 Oil Filter Socket, Size 99mm waf

Applicable to Toyota Diesel etc.

Suitable for use on oil filters with size 99mm waf and 15 flats.

#### KL-0122-426





# KL-0122-426 Oil Filter Socket,

Size 86mm waf, 16 flats (reinforced design)

Applicable to Volvo, e.g S40, S70 etc.

This oil filter socket is needed to remove/install the oil filter cover when replacing the oil filter cartridge.

Suitable for use on oil filters with size 86mm waf and 16 flats.

**Drive:** 3/8"□

# **GEDORE**








# KL-0122-301 - KL-0122-327







# KL-0122-3.. - Oil Filter Sockets

	KL-0122-31 K Oil Filter Socket Set composed of	of: -	$\neg$
1	KL-0122-32 K Oil Filter Socket Set composed of: -	$\neg$	1
Part No.	Filter Sizes and Application Examples:		
KL-0122-301	74mm waf• 14 flats • 1-step collar design Applicable to Audi,e.g. A1, A3 (TDI); BMW 3 Series (E36 with 4-cylinder engine); Citroën; Fiat; Ford; Lancia; Mazda; Mercedes, e.g. CDI engines, C-and E-Class (with 4-cylinder or 6-cylinder Petrol engine); Mitsubishi; Nissan; Opel/Vauxhall; Peugeot; Porsche; Renault; Toyota; VW, e.g. Golf (IV TDI), up!, Scirocco III, Touran 1T1/1T2 etc.		•
KL-0122-302	74mm waf• 15 flats • 2-step collar design Applicable to Ford, Opel/Vauxhall, Saab etc.		•
KL-0122-303	76mm waf• 15 flats • 2-step collar design Applicable to VW-Audi, Mercedes, Opel/Vauxhall, Ford Focus III etc.		•
KL-0122-304	91mm waf• 15 flats • 1-step collar design Applicable to Alfa Romeo, Fiat, Ford, Honda, Mazda, Mitsubishi, Nissan, Opel/Vauxhall, Porsche, Renault, Volvo, VW-Audi etc.		•
KL-0122-305	79mm waf• 15 flats • 1-step collar design Applicable to Ford, Honda, Isuzu, Mazda, Nissan, Opel/Vauxhall, Subaru, Toyota etc.		•
KL-0122-306	74mm Ø • 30 ribs • 1-step collar design Applicable to Ford etc.		•
KL-0122-307	92mm Ø • 36 ribs • 1-step collar design Applicable to Ford etc.		•
KL-0122-308	64mm waf• 14 flats • 1-step collar design Applicable to Fiat, Daihatsu, Mazda, Nissan, Toyota etc.		•
KL-0122-309	65mm waf• 14 flats • 2-step collar design Applicable to Daihatsu, Toyota etc.		•
KL-0122-310	72mm waf• 14 flats • 1-step collar design Applicable to Toyota, Mini Diesel etc.		•
KL-0122-311	67mm waf• 14 flats • 1-step collar design Applicable to Mazda; Mitsubishi; Ford etc.		•
KL-0122-312	86mm Ø • 18 ribs • 1-step collar design  Applicable to VW, e.g. Golf III, Passat (until model year '96 with TDI engine);  Audi, e.g. A6 (until model year '96 with TDI engine 85 kW / 115 bhp);  Renault, e.g. Clio, Rapid and Laguna (1.9 D), Safrane, Espace III (2.1 D) etc.	•	
KL-0122-313	96mm Ø • 18 ribs • 1-step collar design Applicable to Audi, e.g. A4 (with TDI engine); VW, e.g. Touareg (with V 10 TDI engine), Passat (model year '97 upwards, with TDI engine); Renault, e.g. Master (2.5 and 2.8 D / TD, Laguna, Safrane, Espace III (2.2 D), R19, Rapid and Mégane (1.9 and 2.1 D / TD); Opel/Vuaxhall, e.g. Movano (2.5 and 2.8 D / TD) etc.	•	
KL-0122-314	82mm waf• 15 flats • 2-step collar design Applicable to, Mazda, Nissan, Subaru, Toyota etc.		•
KL-0122-315	89mm waf• 15 flats • 1-step collar design Applicable to Isuzu, Mitsubishi etc.		•
KL-0122-316	100mm waf• 15 flats • 1-step collar design Applicable to Mitsubishi etc.		•
KL-0122-317	93mm Ø • 45 ribs Applicable to VW-Audi (TDI 2.4 / 2.6 and 2.8 engines); Nissan X-Trail etc. 66mm Ø • 6 ribs	•	
KL-0122-318	Applicable to Fiat, e.g. Punto, Idea (1.2); Renault, e.g. Clio 1.2, Express, Kangoo, Rapid, Twingo etc.	•	
KL-0122-319	<b>76mm Ø • 12 ribs</b> Applicable to Dacia, e.g. Logan, Sandero; Fiat, e.g. Ducato, Scudo, Ulysee; Mercedes (to all those with Purflux Filter LS 918); Renault, e.g. Mégane, Laguna Espace III, Trafic (1.9 Diesel), Master (1.9 Diesel); Peugeot, e.g. 307; Honda, e.g. Prelude (BA4 2.0 16V Motor); Opel/Vauxhall, e.g. Vivaro etc.	•	
KL-0122-320	Plastic Storage Case for KL-0122-31 K		•
KL-0122-321	108 mm waf • 18 ribs Applicable to Renault, e.g. Espace, Laguna, Master, Safrane, Traffic (2.4 / 2.5 and 2.8 D / TD)	•	
KL-0122-322	106mm waf • 15 flats Applicable to Fiat (e.g. Ducato 2.5 D / TD) etc.	•	
KL-0122-323	74mm waf • 8 flats Applicable to Fiat, e.g. Doblo, Marea, Stilo; Lancia, e.g. Delta etc.	•	
KL-0122-324	92mm waf • 10 flats Applicable to Fiat, e.g. Cinquecento, Coupé, Croma, Panda, Regata, Ritmo, Seicento, Tempra, Ducato (250) and Tipo; Lancia, e.g. Beta, Dedra, Kappa, Monte Carlo, Prisma, Thema and Trevi etc.	•	
KL-0122-326	86mm waf • 16 flats Applicable to BMW, e.g. 320i (E90), 520i (E60), etc; Volvo, e.g. S40, S70 etc.	•	
KL-0122-327	108mm waf • 15 flats Applicable to Volvo, e.g. C70, S70, V70 (TDI Turbo Diesel), 850 (TDI Turbo Diesel) etc.	•	
KL-0122-329 KL-0122-15	Adaptor 1/2" to 3/8"	•	•
KL-0122-15 KL-0122-330	Oil Filter Claw Socket, Ø 65-120mm  Plastic Storage Case for KL-0122-32 K	•	1
INL-U 122-33U	Fiasiic Stolage Case IOI NL-0122-32 N	•	

Each of the KL-0122-31 K and KL-0122-32 K oil filter socket sets is supplied in a plastic storage case.









#### KL-0122-212





KL-0122-213





KL-0122-217





#### KL-0122-219 B





#### KL-0122-3 Oil Filter Socket, Size 74mm waf

Applicable to VW-Audi, BMW, Citroën, Fiat, Ford, Lancia, Mazda, Mercedes, Nissan, Opel/Vauxhall, Peugeot, Porsche, Renault, Suzuki, Toyota, etc.

Essential tools for Audi A3 TDI, VW Golf IV TDI; BMW E36 with 4-cylinder engines; Porsche Cayenne, Boxster, 911; Mercedes CDI engines as well as C- and E-Class with either a 4- or 6-cylinder petrol engine.

Suitable for use on oil filters with size 74mm waf and 14 flats.

**Drive:** ......1/2"□ or 27mm waf

#### KL-0122-212 Oil Filter Socket, Ø 86mm

Applicable to VW-Audi, Seat, Škoda etc.

Essential tool for VW, e.g. Golf III, Passat (until model year '96 with TDI engine); Audi, e.g. A6 (until model year '96 with TDI engine 85 kW / 115 bhp); Renault, e.g. Clio, Rapid and Laguna (1.9 D), Safrane, Espace III (2.1 D) etc.

Suitable for use on oil filters with 86mm Ø and 18 ribs.

#### KL-0122-213 Oil Filter Socket, Ø 96mm

Applicable to VW-Audi, Seat, Škoda etc.

Essential tool for Audi, e.g. A4 (with TDI engine) • VW, e.g. Touareg (with V 10 TDI engine), Passat (from '97 onwards, with TDI engine) • Renault, e.g. Laguna, Safrane, Espace III (2.2 D), R19, Rapid and Mégane (1.9 and 2.1 D / TD), Master (2.5 and 2.8 D / TD) • Opel/Vauxhall, e.g. Movano (2.5 and 2.8 D / TD), etc.

Suitable for use on oil filters with 96mm Ø and 18 ribs.

#### KL-0122-217 Oil Filter Socket, Ø 93mm

Applicable to VW-Audi, Seat, Škoda, Renault etc.

Essential tool for VW-Audi (2.4, 2.6 and 2.8 TDI Diesel engines) and Renault Maxity etc.

Suitable for use on oil filters with 93mm Ø and 45 ribs.

#### KL-0122-219 B Oil Filter Socket, Ø 76mm

Applicable to oil filters with 76mm Ø and 12 ribs as found on VW-Audi, Mercedes, Seat, Škoda, Citroën, Peugeot, Renault, Nissan, Dacia and Suzuki etc. (e.g. filter: Purflux LS 918, MANN W716/1)

Essential tool for Renault, Nissan, Dacia and Suzuki with K9K engine as well as for the Mercedes 6-cylinder petrol engines M102 and M103.

Thanks to the particularly compact design of the oil filter socket, oil filters on Mercedes M102 and M103 engines can be replaced without the need for removing the induction pipe.

The problem with K9K engines is that the alternator is located very close to the oil filter. Thus, there is a risk of causing a short circuit with the alternator charging cable when using a conventional oil filter tool.

The KL-0122-219 B oil filter socket was specifically developed for this type of engines. The socket features a non-conductive surface coating designed to prevent accidental short circuits and, as a result, to allow the oil filter to be loosened and tightened

Suitable for use on oil filters with 76mm Ø and 12 ribs.







#### KL-0122-5 / KL-0122-51 / KL-0122-52





#### KL-0122-500







KL-0122-501







#### KL-0122-59 A





# KL-0122-2 Oil Filter Socket, Size 22mm waf

Applicable to VW-Audi Diesel engines with either a Mann-, Mahle-or Knecht Filter.

# KL-0122-5 Oil Filter Socket, Size 36mm waf

For example, applicable to BMW 1 Series, 3 Series, 5 Series; Mini One, Cooper, Cooper S and VW Touareg, T5; as well as for the Mercedes Diesel engines OM604, OM605, OM606; BMW engines M52 (6-cylinder), M60 (8-cylinder), M70 (12-cylinder); and VW VR6 engines.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

# KL-0122-51 Oil Filter Socket, Size 32mm waf

Applicable to Opel/Vauxhall, e.g with X10XE, X12XE, Y17DT, Y17DTL engines; Mercedes HGVs, e.g. with OM364, OM366 engines; and Škoda Superb.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

Drive: ----- 3/8"

## KL-0122-52 Oil Filter Socket, Size 27mm waf

Applicable to Mercedes, e.g. A-Class (W169), B-Class (W245), C-Class (W204) and Smart.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

# KL-0122-500 Set of Oil Filter Sockets,

Sizes 32mm / 36mm waf

For example, applicable to BMW 1 Series, M52 (6-cylinder), M60 (8-cylinder), M70 (12-cylinder) engines; Mercedes Diesel engines OM604, OM605, OM606 and HGV engines OM364, OM366; Mini One, Cooper, Cooper S; Opel/Vauxhall X10XE, X12XE, Y17DT, Y17DTL engines; Škoda Superb; VW Touareg, T5, VR6 engines.

These oil filter sockets are intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

Scope of Delivery:

Part No.	Description
KL-0122-5	Oil Filter Socket, Size 36mm waf
KL-0122-51	Oil Filter Socket, Size 32mm waf

## KL-0122-501 Set of Oil Filter Sockets

Sizes 32mm / 27mm / 36mm waf

For example, applicable to BMW 1 Series, M52 (6-cylinder), M60 (8-cylinder), M70 (12-cylinder) engines; Mercedes A-Class (W169), Diesel engines OM604, OM605, OM606 and HGV engines OM364, OM366); Mini One, Cooper, Cooper S; Opel/Vauxhall X10XE, X12XE, Y17DT, Y17DTL engines; Škoda Superb; Smart; VW Touareg, T5, VR6 engines.

These oil filter sockets are intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

Scope of Delivery:

Part No.	Description
KL-0122-5	Oil Filter Socket, Size 36mm waf
KL-0122-51	Oil Filter Socket, Size 32mm waf
KL-0122-52	Oil Filter Socket, Size 27mm waf

# KL-0122-59 A Oil Filter Socket Wrench, Size 27mm waf, Ford

Suitable for use on the following TwinCam (DOHC) Diesel engines: PSA and Ford 2.0 Hdi and Duratorq TDCi (DW10C), as well as PSA, Ford and Jaguar 2.2 Hdi and Duratorq TDCi (DW12C). For example, fitted to Peugeot 308, 3008, 5008, 407, 407 Coupé, 508, RCZ; Citroën C4 Picasso, C5, C5 Mk2, C8, DS4, DS5; Ford Mondeo Mk3, C-Max, Galaxy Mk2, Galaxy Mk3, S-Max, Kuga and Jaguar XF 2.20 Sportbrake.





Note: The torque wrench is not included in the scope of delivery.

#### Accessories: 4549-05 TORCOFIX K





KL-0122-601/KL-0122-602





KL-0122-7



### KL-0122-3300 K Set of Oil Filter Sockets, in a Plastic Storage Case

Universal application. The set covers most vehicles equipped with a paper oil filter and either a plastic or metal screw cap.

When installing the oil filter, the plastic or metal screw cap **must** be tightened to a given torque.

Non-observance can lead to damage to the plastic screw cap. The **KL-0122-3300 K** oil filter tool set with its 6 oil filter sockets, together with the **4549-05** torque wrench (accessory), is the perfect solution for this job.

Universally applicable, e.g. for: •VW-Audi, e.g.: TDI ⇒ Golf III, Passat, A4;TDI PD ⇒ A2, A3, A4, A6, TT, Lupo, Polo, Golf IV/V, Passat, Sharan, Touareg, T4, T5; •BMW, e.g.: 1 Series (E87), 3 Series (E36, E46), 5 Series (E39, E60), 7 Series (E38, E65), Z3, Z4, X3, X5; •Mini, e.g.: Mini One, Cooper, Cooper S; •Mercedes, e.g.: A-, C-, E- und S-Class, as well as Sprinter; •Opel/Vauxhall, e.g.: Agila, Astra G / H, Corsa C, Meriva, Signum, Vectra B / C, Zafira.

#### Scope of Delivery (KL-0122-3300 K):

Part No.	Description
KL-0122-301	Oil Filter Socket, Size 74mm waf, 14 flats
KL-0122-313	Oil Filter Socket, 96mm Ø 18 ribs
KL-0122-326	Oil Filter Socket, Size 86mm waf,16 flats
KL-0122-5	Oil Filter Socket, Size 36mm waf
KL-0122-51	Oil Filter Socket, Size 32mm waf
KL-0122-52	Oil Filter Socket, Size 27mm waf
KL-0122-3390	Plastic Storage Case (empty)

Accessories: 4549-05 - TORCOFIX K Code: 1545140 5-50 Nm, Length: 335mm, graduation: 0.25 Nm, Weight: 540g

### KL-0122-601 Oil Filter Socket,

Ø 66mm, 6 Ribs

Suitable for use on Renault vehicles such as Twingo, Clio (with a D petrol engine and filter no. 77 00 869 029).

Suitable for use on oil filters with 66mm Ø and 6 ribs. This socket allows for the quick and easy removal of stuck oil filters.

#### KL-0122-602 Oil Filter Socket,

Ø 108mm, 18 Ribs

Suitable for use on Renault vehicles such as Trafic, Master, Safrane (with an S8U engine and filter no. 77 00 860 823).

Suitable for use on oil filters with 108mm  $\emptyset$  and 18 ribs. This socket allows for the quick and easy removal of stuck oil filters.

### KL-0122-7 Oil Filter Wrench, Ø 76mm, 12 Ribs

Applications:

Ford with a 1.8 Diesel engine and Motorcraft filter EFL 344 Peugeot with Purflux filters

Renault, e.g.: R5, Twingo, Rapid (with C Petrol engines); Clio, Kangoo (with E Petrol engines); R19, Espace III, Laguna (with F Petrol engines); Megane, Kangoo (with K Petrol engines, only those with filter No. 77 00 873 583); R21, Espace I + II (with F-Petrol engine); Trafic (with J Petrol engine, only those with filter No. 77 00 720 978) Honda, e.g. Prelude (BA4 2.0 16V)

Land Rover Defender 2.5 Diesel (DD5) with filter No. LPX 100 590, etc.

Suitable for use on oil filters with 76mm  $\varnothing$  and 12 ribs. This socket allows for the quick and easy removal of stuck oil filters.





#### KL-0122-609





KL-0122-611






KL-0122-606





KL-0122-651





KL-0122-605





KL-0122-12





## KL-0122-612 Oil Filter Socket, Size 73mm waf, 10 Flats

#### Suitable for use on Alfa Romeo GTA.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

## KL-0122-609 Oil Filter Socket, Size 84mm waf, 14 Flats

For example, applicable to Mercedes OM642 CDI engines as found in: C-Class (320), CLS (320), E-Class (280, 320), S-Class (320), ML (280, 320), etc.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

### KL-0122-611 Oil Filter Socket, Size 103mm waf, 14 Flats

Suitable for use on 3.0 litre Diesel engines as found in Opel/Vauxhall Signum (Z30DT; Y30DT) and Renault Espace (IV), VEL Satis etc.

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

## KL-0122-606 Oil Filter Socket, Size 106mm waf, 15 Flats

For example, suitable for use on the MAN 8-10t Series L2000, LE, M2000 and ME. (MANN Filter No. W 1160)

This tool allows stubborn and hard-to-reach oil filters to be removed and installed quickly and with ease.

**Drive:**......1/2"□

## KL-0122-651 Oil Filter Socket, Size 106mm waf, 15 Flats

For example, suitable for use on the MAN 8-10t Series L2000, LE, M2000 and ME. (MANN Filter No. W 1160)

This tool allows stubborn and hard-to-reach oil filters to be removed and installed quickly and with ease.

## KL-0122-605 Oil Filter Socket, Size 135mm waf, 18 Flats


For example, suitable for use on the MAN 18-48t Series F2000, FE and TGA. (MANN Filter No. HU 1381 x)

This oil filter socket is intended for the removal and installation of the oil filter cover when replacing the oil filter cartridge.

## KL-0122-12 Oil Filter Socket, Ø 60-125mm

#### Intended for use on oil filters with Ø of 60-125mm.

Allows the user to loosen oil filters quickly and safely. Retaining jaws grip the filter without risk of slipping. The ideal tool when space is at a premium.



## KL-0122-13 Oil Filter Socket, Ø 64-80mm

The socket allows for the quick and safe loosening of oil filters found on European vehicles. Retaining jaws grip the filter without risk of slipping. The ideal tool when space is at a premium.

 Clamping range:
 Ø 64-80mm

 Drive:
 3/8"□

# KL-0122-14 Oil Filter Socket, Ø 80-98mm

Like the **KL-0122-13**, however with:

 Clamping range:
 Ø 80-98mm

 Drive:
 3/8"□

# KL-0122-191 Oil Filter Socket (universal), Ø 60-80mm

Universally suitable for use on oil filters with  $\emptyset$  of 60-80mm as found in passenger cars.

Allows the user to loosen oil filters quickly and safely. Retaining jaws grip the filter without any risk of slipping. The ideal tool when space is at a premium.

 Clamping range:
 Ø 60-80mm

 Drive:
 1/2"□ or 21mm waf

# KL-0122-192 Oil Filter Socket (universal) Ø 80-110mm

Universally suitable for use on oil filters with  $\emptyset$  of 80-110mm as found in passenger cars.

Allows the user to loosen oil filters quickly and safely. Retaining jaws grip the filter without any risk of slipping. The ideal tool when space is at a premium.

 Clamping range:
 Ø 80-110mm

 Drive:
 1/2"□ or 22mm waf

### KL-0122-193 Oil Filter Socket (universal) Ø 110-145mm

Universally suitable for use on oil filters with  $\emptyset$  of 110-145mm as found in HGVs.

Allows the user to loosen oil filters quickly and safely. Retaining jaws grip the filter without any risk of slipping. The ideal tool when space is at a premium


 Clamping range:
 Ø 110-145mm

 Drive:
 1/2"□ or 24mm waf


KL-0122-193














# "Swivel Grip" Oil Filter Wrenches

Designed to loosen oil filters.

Self-adjusting mechanism allows the stainless steel band to readjust itself while loosening the filter. Swivel handle can be angled up to  $90^\circ$  via a pivot joint. THE ideal tool for use in confined spaces.

Part No.	Description	Clamping range	Weight
KL-0122-801	Oil Filter Wrench	Ø 60-66mm	310g
KL-0122-802	Oil Filter Wrench	Ø 73-82mm	370g
KL-0122-803	Oil Filter Wrench	Ø 89-98mm	370g
KL-0122-804	Oil Filter Wrench	Ø 105-112mm	400g

## KL-0122-40 Oil Filter Belt, (for Ø of up to 152mm)

#### Suitable for filters featuring a diameter of up to 152mm.

Adjusts itself infinitely to fit any oil filter up to a diameter of 152mm.

Drive:	½" 🗆
Weight:	

# KL-0122-851 Oil Filter Pliers, Ø 57-100mm

#### Suitable for HGVs, tractors, etc.

Thanks to its 2-stage adjustment feature, the tool covers an application range of from 57 to 100mm. For better handling, the jaws are angled by 20°. The hardened teeth prevent the tool from slipping.

Clamping range:	Ø 57-100mm
Weight:	560g

# KL-0122-852 Oil Filter Pliers, Ø 92-152mm

Suitable for big oil filters, for example for those fitted to HGVs, tractors, etc.

Thanks to its 2-stage adjustment feature, the tool covers an application range of from 92 to 152mm diameter. For better handling, the jaws are angled by 20°. The hardened teeth prevent the tool from slipping.

Clamping range:	Ø 92-152mm
Weight:	760g

## KL-0231-30 Oil Filter Wrench

Suitable for the all-wheel-drive vehicles VW Bora, Golf (IV and V), Sharan, Touran 4motion as well as Audi A3 and TT Quattro etc.

Designed to remove and install the Haldex clutch oil filter.

Length:	. 400mm
Weight:	700g

**GEDORE** 



#### KL-4041-3045 Screwdriver Bit Socket, T45

For example, suitable for use on Opel/Vauxhall.

Designed to loosen and tighten the Torx® T45 oil drain plugs.

Weight: ..... 85g

Length: ..... 55mm **Drive:** ..... 1/2"□

#### KL-0231-2 Multi-Spline Socket, XZN, M16

Applicable to Audi A3, A4, A6; VW Fox, Golf (IV), LT.

This multi-spline socket features an inner bore and is therefore the ideal tool for oil drain plugs and oil control plugs on gearboxes.

1/2"□ Drive:

#### KL-0231-1 Articulated Socket, Hexagonal, Size 17mm waf

Intended for use on gearbox oil control plugs on manual transmissions on **VW** and **Audi** passenger cars. Also ideal for use on VW Golf II and III as well as Audi vehicles with **automatic transmission** where the oil control plug at the gearbox is hard to access.

**Drive:**..... 3/8"□

## KL-0122-901 K Oil Service Tool Set

Set of Oil Service Tools (12-piece) for the loosening and tightening of virtually any type of oil drain plugs that are commonly used today Composed of:

Part No.	Description	Qty
KL-0122-9001	T-Bar, with 3/8" Drive	1
KL-0122-9002	Socket, © 3/8"	1
KL-0122-9003	Socket, ® 8mm	1
KL-0122-9004	Socket, 9mm	1
KL-0122-9005	Socket, 10mm	1
KL-0122-9006	Socket, 12mm	1
KL-0122-9007	Socket, 14mm	1
KL-0122-9008	Socket, 17mm	1
KL-0122-9009	Socket, ■ 5/16"	1
KL-0122-9010	Socket, ■ 3/8"	1
KL-0122-9011	Socket, ■ 11mm	1
KL-0122-9012	Socket, 13mm	1
KL-0122-9019	Plastic Storage Case	1

#### KL-0122-902 Oil Service Tool, Size (waf) 8mm/10mm (square)

#### Applicable to e.g. Citroën, Renault, Peugeot etc.

Designed to loosen and tighten the oil drain plug at the engine. Also intended for use on the control plug at the gearbox/differential.

**Length:**......220mm Weight:.....350g Waf Size (external square) ......8 and 10mm

### KL-0132-48 K Repair Kit for M14x1.5 Oil Drain Plug Thread

This repair kit is designed to repair the M14x1.5 oil drain plug retaining thread at the oil sump. The special tap included in the kit allows the old thread to be drilled out and a new M15x1.5 sump plug retaining thread to be recut at the same time.

#### KL-0362-1 Set of Blanking Plugs (External Thread)

Suitable for use on all Mercedes passenger cars equipped with an automatic gearbox and an oil cooler for transmission fluid.

When removing the oil cooler, these plugs are necessary in order to prevent any spillage of the Automatic Transmission Fluid.

Thread: M16x1.5



Mercedes

KL-0362-1



# **GEDORE Automotive GmbH**

Breslauer Straße 41 78166 Donaueschingen Postfach 1329

78154 Donaueschingen - GERMANY

T+49 (0) 771 / 8 32 23-0 F +49 (0) 771 / 8 32 23-90 info@gedore-automotive.com

www.gedore-automotive.com

Only for USA, Canada & Mexico Sólo para EE.UU., Canadá y México Seulement pour les USA,

le Canada et le Mexique

**GEDORE TOOLS, INC.** 

7187 Bryhawke Circle, Suite 700 North Charleston, SC 29418

USA

Phone +1-843 / 225 50 15 Fax +1-843 / 225 50 20 info@gedoretools.com

# **GEDORE WELTWEIT GEDORE WORLDWIDE**

Weltweite GEDORE Servicestellen / Niederlassungen finden Sie im Internet unter: www.gedore.com

Worldwide GEDORE service centers / offices are listed on the Internet at: www.gedore.com