



MKS 18 LTX BL 58

- Powerful Brushless motor for quick work progress and highest efficiency
- Powerful cordless metal cutting circular saw with chip collection box for cold sawing of metals. Compatible with guide rails.
- Fast and precise cutting of tubes, profiles, channels, metal grids and sheets, free from sparks and burrs.
- With chip collection box for a clean working environment
- Robust saw with guard made from die-cast aluminium and stainless steel base plate
- Lower weight and compact, ergonomic design
- Viewing window in the guard for precise cutting guidance
- Cutting depth control, steplessly adjustable and without tools according to mm and inch scale
- Comfortable saw blade change with spindle lock
- Fast brake for highest safety with quick saw blade stop (< 1 sek)
- Precise straight cuts of metal grids, steel and profile sheets thanks to guide rail (accessory)
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600773840
EAN code	4061792264656

Type of battery pack	LiPOWER / LiHD
Battery voltage	18 V
Adjustable cutting depth	0 - 58 mm // 0 - 2.28 "
Maximum cutting depth at 90°	58 mm / 2.28 "
Saw blade Ø x bore	165 x 20 mm // 6 1/2 x 5/8 "
Max. cutting speed	1.34 m/min / 52.75 inch/min
Weight without battery pack	2.8 kg / 6.2 lbs
Weight with battery pack	3.8 kg / 8.4 lbs

Scope of delivery

Carbide circular saw blade for metal (40 teeth), Parallel guide, Hexagonal wrench, Guide rail adapter, metaBOX 340, without battery pack, without charger