



ASCD 18-1000 W34 AS

Cordless impact wrench/driver

Up to max. 1050 Nm with brushless motor and 6-stage torque setting. For metric screwdriving applications up to M27.

Part number: 7 115 12 61 00 0

FEIN benefits

- > For extreme precision work: The ASCD 18-1000 W34 AS with electronic torque setting (6 levels) prevents screw heads from shearing off.
- > VARIO 3/4" adapter, available as an extra and developed by FEIN. Suitable for all VARIO accessories for simple and mechanical drilling, countersinking, tapping, recutting and cleaning through threads up to a maximum of M30. Turns the impact wrench/driver into a tapper, thereby adding a whole new tool to the range of applications.
- > Brushless FEIN PowerDrive motor with 30 % higher efficiency and long service life.
- > 3/4" square head for holding sockets.
- > High torque of up to 1050 Nm for tightening and loosening screws of up to M27.
- > Maximum release torque of 1500 Nm in reverse running.
- > Robust solid metal impact gear.
- > Up to 600 screw connections (M27) with one battery charge (ProCORE 8.0 Ah).
- > Compatible with Bosch Professional 18 V batteries (available since 2008) and AMPShare batteries.
- > Maximum work progress with AMPShare 18V ProCORE batteries: COOLPACK 2.0 technology delivers a 135% longer battery life. State-of-the-art cell technology and intelligent battery management deliver 87% more power than with conventional batteries. "Electronic Cell Protection" (ECP) protects the battery from overload, overheating and total discharge.
- > Ideally equipped for every job. Mobile working with the L-BOXX system.

Supplied



1 tool case (L-BOXX 136)



Technical data

GENERAL TECHNICAL DATA

Battery voltage	18 V
Battery compatibility	Li-ion / ProCORE Li-ion
Battery interface	18 V AMPShare
Motor	brushless
Speed, no load	0 - 1 800 rpm
Impacts	0 - 2 200 rpm
Max. torque	1 050 Nm
Torque levels	6
Tool Holder	3/4 in Outer square
Max. metric screw	M27 (8.8)
Wood screw Ø	12 x 600 mm
Weight without storage battery	3.10 kg

VIBRATION AND NOISE EMISSION VALUES

Sound pressure level LpA	96,7 dB
Uncertainty of measured value KpA	3 dB
Sound power level LWA	104,7 dB
Uncertainty of measured value KWA	3 dB
Sound peak value LpCpeak	121,3 dB
Uncertainty of measured value KpCpeak	3 dB
Vibration value 1 dhv 3-way	ah 15,7 m/s ²
Uncertainty of measured value Kα	1,5 m/s ²

Examples of use



Powered by



BOSCH

**Kompatibel mit
AMPSHare-/ Bosch
Professional 18 V
Akkus.** | Compatible
with AMPSHare/Bosch

Professional 18 V batteries. | Compatible avec
les batteries 18 V AMPSHare/Bosch Professional. |
Compatible con baterías AMPSHare/Bosch
Professional de 18 V. | Compatibile con le batterie
AMPSHare / Bosch Professional da 18 V.

