


KERN BFC 6T-3M

KERN

Floor scale with screwed-on weighing plate (IP67), verification optional



Category	
Brand	KERN
Product category	Industrial scale
Product group	Floor scale
Product family	BFC

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	6000 kg
Readability [d]	2 kg
Reproducibility	2 kg
Linearity	± 2 kg
Minimum weight [Min]	40 kg
Resolution	3.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6000 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Linearisation in dots	2
Eccentric loading at 1/3 [Max]	2 kg
Default unit	kg
Units	kg
	g
	ffa
	PCS
	%
Units (if device is conformity assessed)	kg g
Conformity assessment possible	✓
Loadcell type	ZEMIC H8C 2.5 ton
Load cell connection	6-wire

Display	
Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction	
Dimension display device (W×D×H)	220×150×66,5 mm
Dimensions weighing surface (W×D)	1500×1500 mm
Dimensions weighing surface	1500×1500 mm
Dimensions weighing platform (W×D×H)	1500×1500×123 mm
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Material display housing	Plastics
Material load cell(s)	alloyed steel
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	5 m
Platform Construction	Welded load plate; chequer plate
Load cells - number	4

Functions	
PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	3.000

KERN BFC 6T-3M



Floor scale with screwed-on weighing plate (IP67), verification optional

Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	2 kg
Smallest piece weight when piece counting - normal conditions	20 kg
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	IP67
IP protection - load cell	IP67
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional)
	analogue (4 - 20 mA) (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
KUP	
WiFi (optional)	
EasyTouch (ET) - Compatibility	vollständig
EasyTouch (ET) - Connection type	KUP

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK

	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Battery / accumulator type	Li-Ion
Battery	no battery
Rechargeable battery operating time - backlight on	11 h
Rechargeable battery operating time - backlight off	22 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	2 kg

Services (optional)

Article number for adjustment at the location of installation	961-252
Article number for conformity assessment	965-232
Article number for DAkkS calibration	963-132
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1615×1580×360 mm
Shipping method	Freight
Net weight approx.	225 kg
Gross weight approx.	290 kg
Shipping weight	287 kg


KERN BFC 6T-3M



Floor scale with screwed-on weighing plate (IP67), verification optional

Pictograms

STANDARD



OPTION



FACTORY

