


KERN BXC 1.5T-4M



Stainless steel floor scale with screwed-on weighing plate (IP67) and stainless steel display device (IP68), verification optional



Load cell connection	6-wire
----------------------	--------

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	232×150×77,3 mm
Dimensions weighing surface (W×D)	1500×1250 mm
Dimensions weighing surface	1500×1250 mm
Dimensions weighing platform (W×D×H)	1500×1250×85 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	stainless steel
Material load cell(s)	Stainless steels
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	5 m
Platform Construction	Screwed load plate; smooth surface (unscrewable)
Load cells - number	4

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓

Category

Brand	KERN
Product category	Industrial scale
Product group	Floor scale
Product family	BXC

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	1500 kg
Readability [d]	0,5 kg
Reproducibility	0,5 kg
Linearity	± 1,5 kg
Minimum weight [Min]	10 kg
Resolution	3.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1500 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Linearisation in dots	2
Eccentric loading at 1/3 [Max]	2,5 kg
Default unit	kg
Units	kg g ffa PCS %
Units (if device is conformity assessed)	kg g
Conformity assessment possible	✓
Loadcell type	ZEMIC BM8H 1 ton

KERN BXC 1.5T-4M



Stainless steel floor scale with screwed-on weighing plate (IP67) and stainless steel display device (IP68), verification optional

Counting resolution (laboratory conditions)	3.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	500 g
Smallest piece weight when piece counting - normal conditions	5 kg
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	IP68
IP protection - platform	IP67
IP protection - load cell	IP68
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional, factory)
	Ethernet (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional, factory)
	analogue (4 - 20 mA) (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
	USB-Device (optional, factory)
EasyTouch (ET) - Compatibility	vollständig
EasyTouch (ET) - Connection type	KUM

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO

Input voltage power supply / power [Max]	110 V - 240 V AC
Battery / accumulator type	Li-Ion
Battery	no battery
Rechargeable battery operating time - backlight on	11 h
Rechargeable battery operating time - backlight off	22 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,5 kg

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1615×1330×345 mm
Shipping method	Freight
Net weight approx.	150 kg
Gross weight approx.	205 kg
Shipping weight	202 kg


KERN BXC 1.5T-4M

KERN

Stainless steel floor scale with screwed-on weighing plate (IP67) and stainless steel display device (IP68), verification optional

Pictograms

STANDARD



OPTION



FACTORY

