

KERN OIV 901



The entry level video microscope with bright image reproduction and intuitive operation



Category	
Brand	Optics
Product category	Microscope
Product group	Video microscope
Product family	OIV-9

Display	
Display type	LCD
Display screen size	12"
Display resolution	1920×1080 HD

Languages of the user interface	German
	English
	French
	Spanish
	Italian
	Russian

Construction	
Dimension (W×D×H)	320×260×450 mm
Dimension display device (W×D×H)	280×170×12 mm
Material display housing	Plastics
Optical system	Axial
Tube type	Trinocular
Contrasting methods	Bright field

Functions	
Camera - Applicable software	integrated
Camera - Software functions	Image capturing
	Video capturing
	Image editing/
	Documentation
Memory - total size	Measurements
	32 GB

Interface	
Interfaces	USB 2.0
	HDMI
	MicroSD card slot

Objective	
Objectives magnifications	0,7 x - 4,5 x

Illumination	
Illuminance	Reflected light
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination dimmable	Incident light

Focussing	
Field of view [Min]	2,5 mm
Field of view [Max]	16 mm
Zoom [Min]	0,7 x
Zoom [Max]	4,5 x
Sample height [Max]	110 mm
Torque regulation	✓
Working distance	100 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand	
Stand type	universal (jointed arm with clamp)
Diameter mounting universal stand (Ø)	37 mm
Diameter mounting microscope head (Ø)	76 mm
Arm length	553 mm

Camera	
Cameratype	integrated tablet-camera
Camera - Resolution	5 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,8"
Camera - Framerate	60 fps
Camera - Exposure method	Rolling Shutter

Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply type	Table power supply (separable)

KERN OIV 901



The entry level video microscope with bright image reproduction and intuitive operation

Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 2000 mA

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval	
CE mark	✓

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	420×390×250 mm
Shipping method	Parcel service
Net weight approx.	4,4 kg
Gross weight approx.	6 kg
Shipping weight	8,2 kg

Pictograms

STANDARD

