

# KERN YKC-01

Reliable thermal printer for standard applications

# KERN



## Category

Brand	KERN
Product category	Balance
Product group	Printer
Product family	YKC

## Construction

Dimension (W×D×H)	125×125×150 mm
Material	plastic

## Interface

Interfaces	RS-232 standard
------------	-----------------

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	24V 2.5A

## Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Humidity of environment [Min]	20 %
Humidity of environment [Max]	85 %
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

## Approval

CE mark	✓
---------	---

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	220×215×150 mm
Shipping method	Parcel service
Net weight approx.	0,80 kg
Gross weight approx.	1,4 kg
Shipping weight	1,4 kg

## Pictograms

### STANDARD

