

300H04S6 Hand punch stamp with 6-line star, 4 mm font size, 58 - 61 HRC hardness at the engraving



DESCRIPTION

The hand punch stamps with a 6-line star of the 300 series are used for easy marking of workpieces with a strength of up to 900 N/mm² (27 HRC) in craft, industry, and workshop. The stamps have a hardness of between 58 and 61 HRC at the engraving. The stamps are particularly suitable for text and serial number limitation on type plates.

RANGE OF APPLICATION

For easy marking of workpieces with a strength of up to 900 N/mm² (27 HRC)

BENEFIT

- Font height adjusted to the font style
- To enable the most precise impact, the punch is ground on all sides up to the engraving.
- Thanks to CNC technology, milled with the highest precision

OPERATION

- Set the stamp and use a hammer to emboss it into the material

MASTER DATA

GTIN [EAN]	4027474222376
Country of origin	DE
Case material	Tool steel
Series	300H-S6
Net weight [kg]	0,45 kg
Package contents	1 piece
Packaging Act	PAP 20
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)