

476K0300-140 Heavy U-clamp with toggle grip, max. 300 mm clamping range, 140 mm clearance



DESCRIPTION

The heavy U-clamps with screw handle of the 476K series are used for clamping T- and double-T steel beam profiles in the industry. The heavy U-clamp also withstands the required increased performance, making it suitable for use in tough conditions.

RANGE OF APPLICATION

For clamping on T and double-T steel beam profiles

BENEFIT

- Clamping force up to 11,000 N
- Pressure plate with integrated spindle lock prevents loosening during vibrations on the workpiece
- Smooth-running trapezoidal spindles ensure even higher power transmission

OPERATION

- Place the fixed arm against the workpiece to be held and roughly fix it by moving the sliding arm
- Tighten the spindle by operating the handle to firmly fix the workpiece in place

MASTER DATA

GTIN [EAN]	4027474032968
Country of origin	DE
Case material	Tool steel
Series	476K
Net weight [kg]	3,665 kg
Package contents	1 piece
Packaging Act	PAP 21
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)