

1900-30 European with double-sided jaw, 14 mm jaw width, up to 30 mm clamping range



DESCRIPTION

The European of the series 1900 is used for compressing and holding multiple workpieces in craft, industry, and workshops. The adjustable spanner with double-sided jaw can easily fix both metallic and round or multi-edged bodies. It is an evolution of the "French" and "British". In addition to its holding activity, it can also be used for clamping, fixing, screwing, or loosening.

RANGE OF APPLICATION

For pressing together and holding several workpieces

BENEFIT

- No uncontrolled adjustment due to locking mechanism
- Single-sided jaw opening for improved usability
- Removable grip-friendly soft plastic caps are particularly gentle on metallic objects
- Locked-Unlocked-System prevents slipping

OPERATION

- Fix workpiece with rhombic or flat jaw and clamp tightly.

MASTER DATA

GTIN [EAN]	4021176000355
Country of origin	DE
Case material	Tool steel
Series	1900
Net weight [kg]	0,455 kg
Package contents	1 piece
Packaging Act	PAP 21
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)

SPARE PARTS

- 19030010-GR_Protection cap for European

APPLICATION IMAGE

