

YRH-206 Hollow piston cylinder with max. 20 t tension force, 150 stroke



DESCRIPTION

The hydraulic hollow piston cylinders of the YRH series are used with the KUKKO hydraulic programme in crafts, industry, and workshops. They can be used both as pressure cylinders and as tension cylinders, thereby enabling force-saving and versatile work even in difficult pulling situations or when a lot of force is required.

RANGE OF APPLICATION

For use with the KUKKO hydraulic program in craft, industry, and workshop.

BENEFIT

- All models come with a CR-400 coupling sleeve with dust cap
- External thread on the cylinder head, internal thread of the piston rod, and mounting thread on the cylinder base enable easy assembly.
- The preloaded return spring increases retraction speed and thus enhances performance
- The integrated wiper removes contaminants from the piston, thus extending the cylinder's service life.

OPERATION

- Remove dust cap
- Connect hydraulic hose to pump and screw in the threaded sleeve by turning the union nut
- Gently move the connected parts to check the connection for safety

MASTER DATA

GTIN [EAN]	4021176870934
Country of origin	DE
Case material	Tool steel
Series	YRH
Net weight [kg]	14,185 kg
Package contents	1 piece
Packaging Act	PAP 21
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)

APPLICATION IMAGE

