



WVBF 18 LT BL 11-125 Quick with brake, speed control, quick-locking nut

- Cordless angle grinder with extremely low gear head for working in acute angles down to 43°
- Brushless cordless angle grinder of the new generation: as powerful as a 1,100 Watt mains-powered tool thanks to 40% more power
- Variable speed setting with thumbwheel for working on materials requiring customised speeds, and at speeds which remain constant under load
- Fast brake system for highest user safety: Disc stops within 1.5 seconds after switching off
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Battery pack can be rotated in 90° steps for best ergonomics in any working position
- Detachable dust filter protects motor from coarse particles
- Electronic overload protection, soft start and restart protection
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601307840
EAN code	4061792263819
Battery voltage	18 V
Minimum accessible angle	43 °
Disc-Ø	125 mm / 5 "
No-load speed	2000 - 8000 rpm
Spindle thread	M 14
Handle circumference	177 mm / 7 "
Weight without battery pack	1.9 kg
Weight with battery pack	2.35 kg

Scope of delivery

5 Flap discs Flexiamant Super Convex (125mm; P60), Guard, Inner support flange, Quick-locking nut, Side handle, Dust Protection Filter, metaBOX 165 L, without battery pack, without charger