



Basic 220-24 OF Silent

- Quiet, comfortable, mobile: silent compressor for universal use with lots of clever details
- Very quiet operation thanks to the innovative design of the aggregate, ideal for use in noise-sensitive environments or small spaces
- Oil-free two-cylinder aggregate for simple transport and low-maintenance operation
- VarioGrip: pull comfortably and save space while working, thanks to the movable clamping yoke with comfort handle
- Everything included: mount for compressed air hose and two compressed air tools, slots for small accessories and practical cable winder on the compressor
- Everything in view: user-friendly display with large pressure gauges for tank and operating pressure, pressure setting and hose connection
- Condor pressure switch for reliable function and regulation
- Overload protection: protects the motor from overheating
- Large wheels and rubberised feet for optimal stability
- Comfortable condensate outlet via ball valve with wing grip
- No testing required before initial operation
- 10 year tank warranty against rust
- Easy setup: smart packaging concept for quick, simple assembly of wheels and rubber feet after unpacking

Order no. EAN code	601593000 4061792270169
Suction rate	220 l/min / 7.7 cfm
Filling capacity	110 l/min / 3.9 cfm
Effective delivery volume (at 80% max. pressure)	95 l/min / 3.4 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	1.1 kW / 1.5 HP
Maximum speed	2800 rpm
Tank capacity	24 l / 6.3 gal
Sound pressure level (LpA)	60 dB(A)
Sound power level (LwA)	80 dB(A)
Dimensions	561 x 330 x 591 mm // 22 3/32 x 13 x 23 1/4 "
Weight	25 kg / 55.1 lbs
Cable length	2.5 m / 98 7/16 "

Scope of delivery

Universal quick-action coupling, Pull handle with rubber-grip