



BS 18 L Set with 74-piece mobile workshop

- Reliable, powerful drill/screwdriver for all standard drilling and screwdriving applications
- Mobile workshop (74 pieces): 5 wood drill bits (4/5/6/8/10mm), 14 HSS drill bits (1.5/1.5/2/2/2.5/3/3/3.5/4/4.5/5/5.5/6/6.5mm), 20 screwdriver bits length 25mm (PH1/PH2/PH2/PH3/PZ1/PZ2/PZ2/PZ2/PZ3/H3/H4/H5/H6/T15/T20/T25/T30/S4/S5/S6), 10 screwdriver bits length 50mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), 10 screwdriver bits length 75mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), bit holder (60mm), 8 socket wrench (6/7/8/9/10/11/12/13mm), countersinks (12.7mm), centering pin (5x100mm), cutter knife with 2 spare blades, measuring tape (3m/10"), pencil (HB), notebook
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no. EAN code	614051710 4061792252219
Type of battery pack	LiPOWER
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Maximum torque, soft	26 Nm / 230 in-lbs
Maximum torque, hard	60 Nm / 531 in-lbs
Adjustable torque	0.7 - 5.5 Nm // 6.2 - 48.7 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	36 mm / 1 13/32 "
No-load speeds	0 - 450 / 0 - 1850 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.6 kg / 3.5 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, 2 LiPOWER Battery Packs (18 V/2.0 Ah), Charger SC 36, Plastic carry case, Accessory set