

# ROPE LIGHT 15

15 m approved rope light providing 15000 lumen

ORIGINAL  
SCANGRIP



SINCE 1906

A cost-effective and versatile LED rope light for convenient illumination on the construction site. It is designed for illumination in stairwells and corridors, and as orientation lights along walkways.

It has a length of 15 meters and provides 15000 lumen. In addition, it offers easy and effortless direct connection to the AC mains.

Compared to other solutions on the market, this rope light features a built-in electronic circuit to ensure compliance with all applicable legislation in the area (EMC directive 2014/30/EU).

Offering a flexible and durable design, the rope light is suitable for humid working environments (IP66) and can operate at temperatures as low as -10 °C.

For convenient storage, the velcro cable strap can be wrapped around the rope light when it is not in use.



**EMC-certified**

Approved by

**TÜV Rheinland**

## TECHNICAL SPECIFICATIONS

SMD LED  
15000 lumen  
120° viewing angle  
200-240 V AC  
135 W power consumption  
IP66  
IK07  
-10 to +40°C

**ROPE LIGHT 15**

Item no. 03.5818

