

Product data sheet

210 28000

Flat Cold Chisel

Chisels for Electric Hammers with SDS max chuck

- For general chiselling and demolition work on masonry, concrete and loose rock
- Small-scale chipping work
- Precise breaking action
- Made of high-alloy tool steel
- Hardened throughout for maximum transmission of striking force
- Cutting edge can be reground
- Meets or exceeds requirements from current (e.g. DIN) standards



General

Article Number	210 28000
EAN	4049002004193
Weight	492 g
Dimension	280 mm
Dimension packaging	305 x 95 x 40 mm

Specifications

Profile	round
Diameter	18 mm
Tip width	25 mm
Manufacturers	AEG, BOSCH, DeWalt, Duss, HILTI, HITACHI, ITW Spit-Impex, Kango, Kress, Makita, Metabo, Milwaukee, Sparky

Classification

eCl@ss 10.1	ADQ284008
ETIM 7.0	EC002833
proficl@ss 7.0	EAA841c002

With reservations regarding technical modifications and errors. Illustration may vary.