

Product data sheet

212 25009 SB

Floor chisels 30° offset

Chisels for Electric Hammers with SDS plus chuck

- For striking off plaster and tiles
- Trouble-free working thanks to the angled design of the chisel blade
- Wide range of applications
- Made of high-alloy tool steel
- Hardened throughout for maximum transmission of striking force
- Cutting edge can be reground
- Meets or exceeds requirements from current (e.g. DIN) standards
- With Euro Holder



General

Article Number	212 25009 SB
EAN	4049002021787
Weight	354 g
Dimension	250 mm
Dimension packaging	325 x 90 x 30 mm

Specifications

Profile	round
Diameter	16 mm
Tip width	40 mm
Manufacturers	AEG, Black & Decker, BOSCH, DeWalt, Duss, HILTI, HITACHI, Kress, Makita, Metabo, Milwaukee, Sparky

Classification

eCl@ss 10.1	ADQ284008
ETIM 7.0	EC002833
proficl@ss 7.0	EAA841c002

With reservations regarding technical modifications and errors. Illustration may vary.