

Product data sheet

502 038 6

Cutters for protective pipe and hose

- For cutting thin-walled plastic pipe (such as plastic protective outer pipe) and plastic and rubber hose, including fabric-reinforced, up to 25 mm outer diameter
- Not for cable cutting
- With opening spring and pawl
- Tool body: plastic, fibreglass-reinforced
- Blade of special tool steel, oil-hardened, replaceable



General

Article Number	502 038 6
EAN	4049002091933
Weight	200 g
Dimension	185 mm
Dimension packaging	82 x 26 x 190 mm

Specifications

Capacity	25 mm
----------	-------

Classification

eCl@ss 10.1	ADG936008
ETIM 7.0	EC000148
proficl@ss 7.0	EAD291c001

Spare Parts

502 038 0 0	Spare blade
-------------	-------------

With reservations regarding technical modifications and errors. Illustration may vary.