

## Product data sheet

# 625 00094 3

## PEW 12 special model

For large ferrules, 95#mm<sup>2</sup>

- Special tool for crimping virtually all crimped connections with conductor cross-sections from 0.08 – 50 mm<sup>2</sup>
- Guarantees exact, solder-free electrical connections
- Parallel crimping jaw closing action
- Optimum leverage
- User-friendly with ergonomic centre of gravity
- One- and two-handed operation
- Wide range of possible combinations



### General

Article Number	625 00094 3
EAN	4049002077876
Weight	680 g
Dimension	200 mm
Dimension packaging	250 x 108 x 43 mm

### Specifications

Finish	black-oxide finish
Grips	reinforced plastic grips
System size	16

### Capacity

Range of applications	Ferrules
Capacity	95.0 mm <sup>2</sup>

### Classification

eCl@ss 10.1	ACD215012
ETIM 7.0	EC000168
proficl@ss 7.0	AAA946c003

*With reservations regarding technical modifications and errors. Illustration may vary.*