

Product data sheet

707 070

MultiStrip® 10 plus



- Cutting, stripping and crimping in a single tool
- Suitable for single- and multi-conductor cables with PVC insulation and a wide range of special insulation types, such as PTFE and rubber insulation
- Insulation strippers adjust automatically to the cross-section and insulation thickness
- Metal clamping jaws hold the cable securely without slipping and without damaging the remaining insulation
- With square crimp function for ferrules, self-adjusting in the range 0.25# - #4#mm²
- Precise and self-adjusting square crimping of ferrules according to DIN 46228 part 1+4
- Consistent crimping quality by forced-lock completion of crimping process
- Interchangeable blade block and length stop
- Glass fibre-reinforced housing, ergonomic two-component grip
- Integrated wire cutter for multi-stranded cables up to 10 mm² and solid up to 6 mm²

General

Article Number	707 070
EAN	4049002151804
Weight	168 g
Dimension	194 x 72 x 18 mm
Dimension packaging	250 x 108 mm

Specifications

Cutting	10.0 mm² / AWG 8
Stripping	0.03 – 10.0 mm² / AWG 32 – 8
Crimping ferrules	0.25 – 4.0 mm² / AWG 22 – 10
Crimping twin ferrules	2x 0.25 – 2.5 mm² / 2x AWG 22 – 14

Classification

eCl@ss 10.1	ACD179012
ETIM 7.0	EC000163
proficl@ss 7.0	AAA000c004

Spare Parts

707 022	Length Stop
707 021	Spare Blade Set

With reservations regarding technical modifications and errors. Illustration may vary.