

Product data sheet

712 100 3

Cable cutter D100



- For cutting single-strand, multi-strand and fine-wire aluminum and copper cables
- Also for lead-coated cables
- Not for steel wire or wire cable
- Ratchet action for high cutting performance
- Telescope arms adjust to a range of lengths
- Cutter can be opened in any cutting position
- Can be used in cramped situations as well as overhead
- Emergency unlock, special cutting contour
- Replacement blades are available for these cable cutting tools.
- Blade replacement work should be completed by RENNSTEIG or by one of our authorised partners.

General

Article Number	712 100 3
EAN	4049002021527
Weight	5,700 g
Dimension	660 mm
Dimension packaging	300 x 70 x 90 mm

Specifications

Finish	black-oxide finish
Max cable dia.	100 mm
Multi-conductor cable (Cu)	Cu 800 mm ²
Multi-conductor cable (AL)	Al 1,000 mm ²
Fine-stranded cable (Cu)	Cu 1,000 mm ²
Sector shaped cable (Cu)	Cu 960 mm ²
Sector shaped cable (AL)	Al 1,200 mm ²
Grips	2-component grips

Classification

eCl@ss 10.1	ADS511008
ETIM 7.0	EC000142
proficl@ss 7.0	EAD256c001

Spare Parts

712 101 3	Spare blade
-----------	-------------

With reservations regarding technical modifications and errors. Illustration may vary.