

**Borestangholder Form E2, VDI 25, Boring d2 (H7): 10 mm****Bestillingsdata**

Bestillingsnummeret	319325 10
GTIN	4045197717597
Artikelklasse	32V

**Beskrivelse****Anvendelse:**

Til indvendig bearbejdning med holder til borestang.

**Norm:**

**DIN 69880 / VDI 3425**, Blatt 2.

Form: E

Farvekode VDI-skaft: VDI 25

l<sub>6</sub>: 50 mm

l<sub>7</sub>: 41 mm

**Teknisk beskrivelse**

Boring d <sub>2</sub> (H7)	10 mm
d <sub>8</sub>	40 mm
l <sub>6</sub>	50 mm
l <sub>7</sub>	41 mm
Form	E
VDI-størrelse	VDI 25
d <sub>6</sub>	58 mm
Farvekode VDI-skaft	VDI 25

Produkttype

VDI-værktøjsholder