



## Bimetalhulsavssortiment Power Change Plus, Type: 19-83



### Bestillingsdata

Bestillingsnummeret	589810 19-83
GTIN	3165140949590
Artikelklasse	54B

### Beskrivelse

#### Udførelse:

Bimetalhulsavssortimentet med Power Change Plus-system med de mest gængse diametre. Inklusive sekskantet holderskaft og HSS-centrerbor i kunststofkuffert.

### Teknisk beskrivelse

Antal centrerbor	2
Antal dele	9
Hulsavs-Ø	19; 25; 38; 44; 68; 83 mm
Antal holdeskafter	1
Serie	Power Change Plus
Produkttype	Hulsav

### Tilbehør

Hulsave, bimetalPower Change Plus Diameter 105 mm	589790 105
Hulsave, bimetalPower Change Plus Diameter 121 mm	589790 121
Hulsave, bimetalPower Change Plus Diameter 152 mm	589790 152
Hulsave, bimetalPower Change Plus Diameter 16 mm	589790 16
Hulsave, bimetalPower Change Plus Diameter 19 mm	589790 19
Hulsave, bimetalPower Change Plus Diameter 20 mm	589790 20
Hulsave, bimetalPower Change Plus Diameter 22 mm	589790 22
Hulsave, bimetalPower Change Plus Diameter 25 mm	589790 25
Hulsave, bimetalPower Change Plus Diameter 29 mm	589790 29
Hulsave, bimetalPower Change Plus Diameter 32 mm	589790 32
Hulsave, bimetalPower Change Plus Diameter 35 mm	589790 35
Hulsave, bimetalPower Change Plus Diameter 38 mm	589790 38
Hulsave, bimetalPower Change Plus Diameter 40 mm	589790 40
Hulsave, bimetalPower Change Plus Diameter 44 mm	589790 44
Hulsave, bimetalPower Change Plus Diameter 51 mm	589790 51
Hulsave, bimetalPower Change Plus Diameter 54 mm	589790 54
Hulsave, bimetalPower Change Plus Diameter 60 mm	589790 60
Hulsave, bimetalPower Change Plus Diameter 65 mm	589790 65
Hulsave, bimetalPower Change Plus Diameter 68 mm	589790 68
Hulsave, bimetalPower Change Plus Diameter 76 mm	589790 76
Hulsave, bimetalPower Change Plus Diameter 83 mm	589790 83
Hulsave, bimetalPower Change Plus Diameter 92 mm	589790 92
HolderskaftPower Change Plus sekskant Passer til hulsave medØ 14-152 mm	589795 14-152
ZentrierbohrerPower Change Plus Type HSS-CO	589800 HSS-CO