

Notlære, Type: B



Bestillingsdata

Bestillingsnummeret	484409 B
GTIN	2050002070950
Artikelklasse	48B

Beskrivelse

Udførelse:

Notlærer med go- og nogo-side. Go-side med **slidovermål** iht. DIN 7164. Læreenhed i hærdet stål.

Notlære med mellem mål og ISO-pasning, f.eks. nr. 484409 str. **15,8 M6**.

Anvendelse:

Til kontrol af fladpasninger f.eks. fra noter.

Norm:

Toleranzen und Abmaße nach **DIN EN ISO 1938-1 und DIN 7164**.

Bemærk:

Størrelsesangivelsen Type beskriver det nominelle mål i millimeter (mm).

Type A = 3,001 – 5,999

Type B = 6,001 – 8,999

Type C = 9,001 – 12,999

Type D = 13,001 – 16,999

Type E = 17,001 – 20,999

Type F = 21,001 – 25,999

Teknisk beskrivelse

Kvalitet	11
Kvalitet	13
Kvalitet	10
Kvalitet	12

Kvalitet	8
Kvalitet	9
Kvalitet	7
Norm	DIN EN ISO 1938-1
Norm	DIN 7164
Nom. mål	6 - 8,999 mm
Tolerancefelt	T
Tolerancefelt	J
Tolerancefelt	S
Tolerancefelt	FG
Tolerancefelt	F
Tolerancefelt	G
Tolerancefelt	ZC
Tolerancefelt	P
Tolerancefelt	N
Tolerancefelt	H
Tolerancefelt	B
Tolerancefelt	Z
Tolerancefelt	CD
Tolerancefelt	C
Tolerancefelt	V
Tolerancefelt	E
Tolerancefelt	K
Tolerancefelt	EF
Tolerancefelt	R
Tolerancefelt	ZA
Tolerancefelt	ZB
Tolerancefelt	U
Tolerancefelt	T

Tolerancefelt	A
Tolerancefelt	D
Tolerancefelt	JS
Tolerancefelt	T
Tolerancefelt	M
Kalibrering	L6
Produkttype	Toleranceaksellære

Services

KalibreringTolerancedorn maks. Ø 20 mm	028300 20
--	-----------