

**Borestangholder Form E2, VDI 25, Boring d2 (H7): 25mm****Bestillingsdata**

Bestillingsnummeret	319315 25
GTIN	4062406754921
Artikelklasse	32U

Beskrivelse**Anvendelse:**

Til indvendig bearbejdning med holder til borestang.

Norm:

DIN 69880 / VDI 3425, Blatt 2.

Teknisk beskrivelse

l_7	51 mm
Boring d_2 (H7)	25 mm
l_6	60 mm
Kølekanalgevind	M8
Spændeskru-gevind	M8
Form	E
VDI-størrelse	VDI 25
d_6	58 mm
Farvekode VDI-skaft	VDI 25
Produkttype	VDI-borestangholder

