

Go-tolerancing, Type: G



Bestillingsdata

Bestillingsnummeret	484037 G
GTIN	4067263129820
Artikelklasse	48B

Beskrivelse

Udførelse:

I førsteklasses lærestål, hærdet, afspændt, slebet og finslebet. Ringe med mellem mål og ISO-pasning, f.eks. nr. 484037 **5,56 h6** eller numerisk tolerance, f.eks. nr. 484037 **28 + 0,01 / -0,02**. Med slidovermål.

Anvendelse:

Glatte ringe til læring af den udvendige diameter.

Norm:

Nach **DIN 2250-G**.

Bemærk:

Ved bestilling skal der angives den nøjagtige nominelle mål-Ø med tolerancefelt (a-zc) og kvalitet (6-13) eller talmæssig tolerance (\pm). Lærer til basistolerancegrad 5 og finere tolerancer fås på forespørgsel.

Teknisk beskrivelse

Kvalitet	6
Kvalitet	7
Kvalitet	8

Kvalitet	9
Kvalitet	10
Kvalitet	11
Kvalitet	12
Kvalitet	13
Norm	DIN 2250-G
Nom. mål	32 - 39,999 mm
Tolerancefelt	a
Tolerancefelt	b
Tolerancefelt	c
Tolerancefelt	cd
Tolerancefelt	d
Tolerancefelt	e
Tolerancefelt	ef
Tolerancefelt	f
Tolerancefelt	fg
Tolerancefelt	g
Tolerancefelt	h
Tolerancefelt	j
Tolerancefelt	js
Tolerancefelt	k
Tolerancefelt	m
Tolerancefelt	n
Tolerancefelt	p
Tolerancefelt	r
Tolerancefelt	s
Tolerancefelt	t
Tolerancefelt	u
Tolerancefelt	v

Tolerancefelt	x
Tolerancefelt	y
Tolerancefelt	z
Tolerancefelt	za
Tolerancefelt	zb
Tolerancefelt	zc
Materiale	Specialstål
Kalibrering	L7
Produkttype	Tolerancing

Services

KalibreringTolerancing maks. Ø 50 mm	028400 50
DAkKS-kalibreringTolerancing maks. Ø 50 mm	028470 50