

**VDI-multiholder, Skaft-Ø d1: 30mm****Bestillingsdata**

Bestillingsnummeret	319185 30
GTIN	4045197955043
Artikelklasse	32V

**Beskrivelse****Utførelse:**

- Indsatshærdet HRC 58 ±2.
- Alle funktionsflader slebne.
- Med kuglesprøjetdyser.

**Norm:**

DIN ISO 10889 / DIN 69880 / VDI 4325, Blatt 2.

**Teknisk beskrivelse**

b <sub>1</sub>	76 mm
l <sub>1</sub>	60 mm
h <sub>1</sub>	20 mm
h <sub>2</sub>	29 mm
h <sub>5</sub>	28 mm
Farvekode VDI-skaft	VDI 30
Skaftbredde b <sub>3</sub>	17 mm
b <sub>2</sub>	35 mm

Skaft-Ø d <sub>1</sub>	30 mm
h <sub>6</sub>	38 mm
Produkttype	VDI-multiholder