

Garant
Side lock arbor Form AD, SK 50 ultra short, Clamping range \varnothing D1: 32mm

Order data

Order number	300412 32
GTIN	
Item class	31A

Description
Version:

Additionally with second locking screw in the slot.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Standard:

Ähnlich DIN 69871.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820; 308830, spare screw No. 309901.

Technical description

Overhang dimension A	70 mm
Clamping \varnothing D ₁	32 mm
External \varnothing D	71.5 mm
Adapter	SK 50 ultra short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Type of product	Side lock arbor