

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 25/16mm

Order data

Order number	251017 25/16
GTIN	4045197711618
Item class	21T

Description
Note:

With KNUX 1604.. Use R insert

Technical description

ISO code toolholder	A25T CKUNR/L16
Clamping claw	259038 16
Screw for clamp	259021 3
Insert size	16 mm
Centre offset L ₃	20.5 mm
suitable indexable insert	KNUX 1604.. R/L
Shim pins pack	259044 3
Minimum pre-drill Ø D _{min}	36 mm
Pin	259049 4
Overall length L	300 mm
Clamping height L ₂	23 mm
Setting angle κ	93 degrees
Shank Ø D _s	25 mm
Standard	Works standard
Application type	left-hand

Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping claw Type 16	259038 16
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Set of shim pins 10 pieces Type 3	259044 3
Pin Type 4	259049 4
Screw for clamping claw Type 3	259021 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600