

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 32/12mm

Order data

Order number	250043 32/12
GTIN	4045197711533
Item class	21T

Technical description

ISO code toolholder	A32U PCKNR/L12
Shim pins pack	259044 2
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Shim punches pack	259047 2
Shim	259031 2
Centre offset L_3	22 mm
Lever	259015 2
Lever screw	259018 2
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Overall length L	350 mm
Clamping height L_2	31 mm
Setting angle κ	75 degrees
Shank $\varnothing D_s$	32 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Lever screw Type 2	259018 2
Lever Type 2	259015 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500