

Garant**Pallet dolly, Platform area width×depth: 1200X800/Hmm****Order data**

Order number	919908 1200X800/H
GTIN	4045197711656
Item class	91T

Description**Version:**

Sturdy steel angle section construction with 4 corner supports to take flat pallets and mesh crates. Resilient solid rubber tyres with 2 fixed wheels and 2 castors (with parking brake) and roller bearing hubs. With handy push handle. Ergonomic handle with Haptoprene® coating for maximum comfort – even with wet or oily hands.

Application:

To take flat pallets and mesh crates.

Colour:

Silver **powder-coated**.

Technical description

Safe working load	1200 kg
Wheel Ø	160 mm
Material of wheel	Resilient solid rubber
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Weight	39 kg

Height	300 mm
Platform area height	245 mm
Width	1275 mm
Platform area width	1210 mm
Platform area depth	810 mm
Depth	875 mm
Push handle	yes
Type of product	Pallet mobility frame