



GÜNZBURGER STEIGTECHNIK

Aluminium work platform with steel grid, Number of steps including platform: 3



Order data

Order number	966149 3
GTIN	4031405510197
Item class	98G

Description

Version:

Sturdy welded tubular design, steps of non-slip steel grid. Stile ends with non-slip plastic end caps. Mobile by means of 2 lift rollers. Upper standing area 550 × 300 mm.

Technical description

Working height approx.	2.6 m
Footprint width	0.73 m
Number of steps including platform	3
Footprint depth	0.97 m
Weight	12 kg
Platform width	550 mm
Rollers	yes
Type of step	Step
Platform depth	300 mm

Accessibility	single-sided
Platform height without railing	0.6 m
Material	welded tubular design, steps of non-slip steel grid.
Ladders and platforms load capacity	150 kg
Type of product	Work platform