

HOLEX**Magnetic measuring stand with fine adjustment at the column, Type: 240****Order data**

Order number	441180 240
GTIN	4045197713193
Item class	42D

Description**Version:**

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard dial indicator mounting for clamping shank \varnothing 6 mm, \varnothing 8 mm and dovetail, fine adjustment at the indicator holder.

Technical description

Magnetic force	800 N
Length of jointed arm L_2	101 mm
maximum loading	4 kg
Length of jointed arm L_1	110 mm
Magnetic base width	50 mm
Magnetic base height	55 mm

Magnetic base length	60 mm
Throat	282 mm
Connection thread at bottom	M8
Type of product	measuring stand

Accessories

Holder for measuring stand Type K2	442100 K2
Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type 2SM	442104 2SM
Stand base Type 1	442140 1
Stand base Type 1	442120 1
Holder for measuring stand Type 2SM	442100 2SM
Stand base Type 0	442140 0
Stand base Type K3	442120 K3
3-D jointed arm Type 240	442114 240
Holder for measuring stand Type H	442100 H
Stand base Type V	442120 V
3-D jointed arm Type 240	442110 240
Stand base Type 1	440868 1
Holder for measuring stand Type CA	442100 CA
Holder for measuring stand Type QR	442100 QR
Stand base Type 0	442120 0
Stand base with fine adjustment Type 0	442125 0