



Side lock arbor, HSK-A 100 short, Clamping range \varnothing D1: 8mm



Order data

Order number	304397 8
GTIN	4045197709196
Item class	32A

Description

Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Overhang dimension A	80 mm
Spare clamping screw No. 30 9900	8
Clamping \varnothing D ₁	8 mm
External \varnothing D	28 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1

Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 8 mm	309900 8
---	----------