



Side lock arbor, HSK-A 100 short, Clamping range \varnothing D1: 32mm



Order data

Order number	304397 32
GTIN	4045197709271
Item class	32A

Description

Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Clamping \varnothing D ₁	32 mm
Overhang dimension A	100 mm
Spare clamping screw No. 30 9900	32
External \varnothing D	72 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1

Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Socket wrench for coolant tubes for HSK 32	309890 32
HSK coolant tube for HSK 32	309880 32
Spare clamping screw for chucks with clamping \varnothing D1 32 mm	309900 32