

**Garant**
**CC.T 120404, Grade: HB7020**


### Order data

Order number	260064 HB7020
GTIN	4045197710819
Item class	21G

### Description

CC.T 120404 HB7020 Grade: HB7020  
 Chip breaker: SS  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 2.5 mm  
 Feed  $f$ : 0.05 - 2.5 mm/rev.  
 Cutting speed  $v_c$  main application: 150 - 400 m/min

### Technical description

Feed $f$	0.05 - 2.5 mm/rev.
Chip breaker	SS
Corner radius	0.4 mm
Cutting speed $v_c$ main application	150 - 400 m/min
Cutting conditions	slightly interrupted
Main application	P
Cutting depth $a_p$	0.2 - 2.5 mm

Grade	HB7020
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 120404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning