

**Garant**

**Countersink set No. 150152 in a case 90°, uncoated, Number of countersinks:  
7**



## Order data

Order number	150312 7
GTIN	4045197717122
Item class	11M

## Description

### Version:

Countersink sets, **in a case.**

Practical set for assembly and workshop use.

**All countersinks have 3 cutting edges**, radially relieved.

Flutes are ground from solid.

Three **drive flats on the shank** for use in a 3-jaw chuck.

### Application:

High precision countersinks for chatter-free countersinking.

### Content:

1× each countersink: Size 6; 8; 10; 11.5; 15; 19; 25

## Technical description

Number of countersinks	7
Number of cutting edges Z	3
Coating	uncoated

Countersink tip angle	90 degrees
Tool material	HSS
Standard	DIN 335 C
Shank	Shank with h9 and three drive flats
Colour ring	without
Type of product	Stepped drill and countersink

---

## Accessories

High-precision countersink90° External Ø Dc 11,5 mm	150152 11,5
High-precision countersink90° External Ø Dc 8 mm	150152 8
High-precision countersink90° External Ø Dc 10 mm	150152 10
High-precision countersink90° External Ø Dc 25 mm	150152 25
High-precision countersink90° External Ø Dc 19 mm	150152 19
High-precision countersink90° External Ø Dc 6 mm	150152 6
High-precision countersink90° External Ø Dc 15 mm	150152 15