



Flexible head wrench, Width across flats: 17X19 mm



Order data

Order number	621405 17X19
GTIN	4045197717368
Item class	62C

Description

Version:

Drop-forged; precisely toleranced jaw widths; bi-hexagon. An integral compression spring keeps the heads in the respective position.

Swivel heads (movement up to 200°).

Material:

Chrome vanadium steel, chrome-plated, smoothed finish.

Spanner length L: 275 mm

Head Ø D₁: 23.7 mm

Head Ø D₂: 25.8 mm

Technical description

Width across flats 1	17 mm
Width across flats 2	19 mm
Head Ø D ₂	25.8 mm
Spanner length L	275 mm
Head Ø D ₁	23.7 mm
Drive profile	Bi-hex socket
Type of product	Socket spanner

