

**Garant**

**Indexable face mill 45° left-hand cutting, with bore, Ø D / number of teeth Z:  
50/5mm**


**Order data**

Order number	214205 50/5
GTIN	4045197717191
Item class	210

**Description**
**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit shank No. **674252 size 20IP**.

**Technical description**

Pack of insert screws	219800 (20IP; 5.7 Nm)
Overall length $L_{tot}$	40 mm
maximum external $\varnothing D_{max}$	63 mm
Cutting edge $\varnothing D_c$	50 mm
suitable indexable insert	SE.. 1204..
Mounting bore $\varnothing$	22 mm
Number of cutting edges Z	5
Shank type	with bore

Setting angle $\kappa$	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	no
Machining strategy	MTC
Type of product	Face mill

---

## Accessories

Set of insert screws 10 pieces	219800
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Torque screwdriver, fixed setting set torque 5,7 N·m	211750 5,7