

Garant
eco parting-off toolholder with ICS, Shank \varnothing d1: 30mm

Order data

Order number	319132 30
GTIN	4045197716781
Item class	31V

Description
Version:

- **With special adjustable ball type coolant nozzle for optimum cooling of the cutting edge, irrespective of the groove depth.**
- **This reduces the temperature both at the main cutting edge and the auxiliary cutting edge, and permits a significant increase in cutting speed.**
- **Rigid toolholder for parting-off tools.**
- **Blade clamped using clamping plate.**

Application:

Allows parting-off tools of different makes to be used.

Note:

Screw plug for ball spray nozzle included. If conventional grooving tools are used, the lateral coolant transfer is blocked by the grooving tool. Suitable clamping claws No. 279840 2 and suitable screws No. 279815 14. See spare parts list.

Technical description

L ₂	70 mm
Colour code for VDI shanks	VDI 30
Shank \varnothing D ₁	30 mm

suitable for blade height	32 mm
L ₁	47 mm
Height H ₁	57.4 mm
Height H ₂	37 mm
Type of product	VDI parting-off toolholder