



## Base body Parallel shank, with through-coolant, 1.5×D, Type: 12



### Order data

Order number	232240 12
GTIN	4045197717726
Item class	22G

### Description

#### Version:

With internal cooling.

#### Straight fluted.

#### Note:

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range  $D_c$ : 12 - 12.5 mm

Reach  $L_1$ : 18.8 mm

Shank  $\varnothing D_s$ : 20 mm

Shank length  $L_s$ : 50 mm

Clamping screws: 232990 TX7

### Technical description

Dia. range $D_c$	12 - 12.5 mm
Shank $\varnothing D_s$	20 mm
Reach $L_1$	18.8 mm
Clamping screws	232990 TX7
Shank length $L_s$	50 mm
Number of cutting edges Z	2
Version	1.5×D

Shank	ISO 9766
Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

Torx® set of screws 10 pieces Drive TX7	232990 TX7
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX7	674248 TX7
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6