



Base body Parallel shank, with through-coolant, 1.5×D, Type: 13



Order data

Order number	232240 13
GTIN	4045197717733
Item class	22G

Description

Version:

With internal cooling.

Straight fluted.

Note:

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 13 - 17.5 mm

Reach L_1 : 26 mm

Shank $\varnothing D_s$: 20 mm

Shank length L_s : 50 mm

Clamping screws: 232990 TX8

Technical description

Clamping screws	232990 TX8
Dia. range D_c	13 - 17.5 mm
Shank $\varnothing D_s$	20 mm
Reach L_1	26 mm
Shank length L_s	50 mm
Number of cutting edges Z	2
Version	1.5×D

Shank	ISO 9766
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx® set of screws 10 pieces Drive TX8	232990 TX8
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3