

SWISS TOOLS

**Boring bar shank, PSC, Shank  $\varnothing$  /  $\varnothing$  D - A dimension: 40/40-120mm****Order data**

Order number	320407 40/40-120
GTIN	2050001772725
Item class	36D

**Description****Version:**

- For efficient turning.
- For left-hand and right-hand turning.

**Application:**

For mounting exchangeable cutting heads.

**Note:**

For suitable interchangeable heads see No. 264826 – 264827.

**Technical description**

Overhang dimension A	120 mm
Shank $\varnothing$	40 mm
$\varnothing$ D	40 mm
Adapter	PSC
Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar base body