

SWISS TOOLS

Boring bar shank vibration-damped, HSK-T, Shank \varnothing / \varnothing D – A dimension: 63/32-185 mm



Order data

Order number	320103 63/32-185
GTIN	2050001772800
Item class	36D

Description

Version:

- For efficient turning.
- For left-hand and right-hand turning.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Through-coolant: yes

Technical description

Overhang dimension A	185 mm
Shank \varnothing	63 mm
\varnothing D	32 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body

