

SWISS TOOLS

Boring bar shank, HSK-T, Shank \varnothing / \varnothing D - A dimension: 40/25-110mm**Order data**

Order number	320102 40/25-110
GTIN	2050001772671
Item class	36D

Description**Version:**

- For efficient turning.
- For left-hand and right-hand turning.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Overhang dimension A	110 mm
Shank \varnothing	40 mm
\varnothing D	25 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body