



GÜNZBURGER STEIGTECHNIK

Aluminium work platform with steel grid, Number of steps including platform: 4



Order data

Order number	966149 4
GTIN	4031405510203
Item class	98G

Description

Version:

Sturdy welded tubular design, steps of non-slip steel grid. Stile ends with non-slip plastic end caps. Mobile by means of 2 lift rollers. Upper standing area 550 × 300 mm.

Technical description

Footprint depth	1.21 m
Platform height without railing	0.8 m
Rollers	yes
Weight	16 kg
Type of step	Step
Material	welded tubular design, steps of non-slip steel grid.
Working height approx.	2.8 m
Platform depth	300 mm

Accessibility	single-sided
Footprint width	0.78 m
Number of steps including platform	4
Platform width	550 mm
Ladders and platforms load capacity	150 kg
Type of product	Work platform