

SWISS TOOLS

**Boring bar shank, HSK-T, Shank  $\varnothing$  /  $\varnothing$  D - A dimension: 40/32-115mm****Order data**

Order number	320102 40/32-115
GTIN	2050001772688
Item class	36D

**Description****Version:**

- For efficient turning.
- For left-hand and right-hand turning.

**Application:**

For mounting exchangeable cutting heads.

**Note:**

For suitable interchangeable heads see No. 264826 – 264827.

**Technical description**

Overhang dimension A	115 mm
Shank $\varnothing$	40 mm
$\varnothing$ D	32 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body