



## Base body MT shank, without through-coolant, 1.5×D, Type: 18



### Order data

Order number	232257 18
GTIN	4045197717863
Item class	22G

### Description

#### Version:

**Straight fluted.**

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: no

Number of cutting edges Z: 2

Dia. range  $D_c$ : 18 - 24 mm

Reach  $L_1$ : 36 mm

Morse taper MT size: 3

Clamping screws: 232990 TX9

### Technical description

Dia. range $D_c$	18 - 24 mm
Clamping screws	232990 TX9
Reach $L_1$	36 mm
Morse taper MT size	3
Number of cutting edges Z	2
Version	1.5×D
Shank	Morse taper
Through-coolant	no
Type of product	Indexable drill

---

## Accessories

Torx® set of screws 10 pieces Drive TX9	232990 TX9
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX9	674248 TX9
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2