

SWISS TOOLS

Boring bar shank, PSC, Shank \varnothing / \varnothing D - A dimension: 50/40-140mm**Order data**

Order number	320407 50/40-140
GTIN	2050001772794
Item class	36D

Description**Version:**

- For efficient turning.
- For left-hand and right-hand turning.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Overhang dimension A	140 mm
Shank \varnothing	50 mm
\varnothing D	40 mm
Adapter	PSC
Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar base body